



Datasheet

MiniPIX TPX3 SPACE

Document Version 1.0.1

Advacam s.r.o. U Pergamenky 12 Prague 170 00 Czech Republic



General features

The **MINIPIX**_{TPX3_SPACE} is a miniaturized, low power radiation camera equipped with Timepix3 chip for particle tracking and imaging.

The Timepix3 detector is position, energy and time sensitive: For each ionizing particle (e.g. X-ray photon) it digitally registers its position, energy, time of arrival and track shape - basically all information you can want. The other measures can be calculated from the track shape (particle type, direction of flight, LET, charge ...). The information on each detected particle is either read-out immediately (pixel mode) or accumulated in images (frame mode) and read out later.

The **MINIPIX**_{TPX3_SPACE} uses LVCMOS 2V5 for communication with a M8 connector.



Advacam's imaging cameras are direct conversion single photon counting pixel detectors that represent the cutting edge of current radiation imaging technology.

SPACE Features

- 256 x 256 square pixels
- 55 µm pixel pitch.
- Timepix3 chip technology
- Up to 16 fps
- Several sensor materials according to customer preference (usually 500 μm thick silicon).
- LVCMOS 2V5
- M8 or Micro-D connector
- Robust housing

- Conformal coating
- Low weight (usually <140 g)
- Low power (2 W)
- Heritage environmental test information

Optional:

- ECSS Soldering
- ISO 8 clean room
- Custom calibration

Advacam s.r.o. U Pergamenky 12 Prague 170 00 Czech Republic



Device parameters

Operating conditions

Symbol	Parameter	Min	Тур.	Max	Units	Comment
T _A	Temperature Range (non-operational)	-25	22	80	°C	
Φ	Humidity (non-operational)	0	55	95	%	Not condensing
T _A	Temperature Range (operational)	-20	22	60	°C	
Φ	Humidity (operational)	0	55	70	%	Not condensing

Warning: Disconnect the device from power during pumping down or venting the vacuum chamber!

Electrical Specification

 $T_A = 25^{\circ}$ C, USB voltage $V_{CC} = 4.8V$

Symbol	Parameter	Min	Тур.	Max	Units	Comment
V _{cc}	Supply Voltage	4.0	5.0	5.5	V	
P1	Power Dissipation		2	3	W	
Bias Voltage Source for Sensor Diode						
V _{BIAS}	Bias Voltage (positive version)	3	80	450	V	With Si sensor
V _{BIAS}	Bias Voltage (negative version)	-4	80	-450	V	With CdTe or CZT senso

Advacam s.r.o. U Pergamenky 12 Prague 170 00 Czech Republic



Enhanced mechanical properties

The SPACE version of the MiniPIX camera incorporates several enhancements to ensure robustness for space applications. The camera has undergone rigorous environmental testing in accordance with ECSS standards, including humidity testing, random vibration testing along all three axes (X, Y, Z), and thermal ambient testing. The tests were conducted with the camera configured with a 500 µm silicon sensor.

Vacuum operation

Advacam detectors are vacuum compatible out of the box. Operate only with air pressure lower than 10-3 Pa. In case of sudden pressure drop, the MiniPIX must be switched off. For Indoor vacuum experiments make sure to disconnect the device from power during pumping down or venting the vacuum chamber!

External cooling

Temperature stabilization is recommended strongly for results. Passive consistent cooling of the device is necessary and can be done by mechanical For active cooling design. attaching a Peltier cooling or cooling plate at the back of the detector should serve the purpose. The temperature should be set to one used for calibration.



The **MINIPIX**_{TPX3_SPACE} is a miniaturized and low power radiation camera equipped with Timepix3 chip for particle tracking and imaging is already on board of the ISS and several satelites.

Advacam s.r.o. U Pergamenky 12 Prague 170 00 Czech Republic